Ultra-Low △P High Performance Mass Flow Control

FEATURES

- Control up to 500 slpm (nlpm) with 4.5 psid (310 mBard)
- High accuracy (+/- 1.0 % of full scale)
- Highly repeatable (+/- 0.2% of full scale)
- True linear performance (+/- 1.0% of full scale in 10 standard gases)
- 10 different gases using Dial-A-Gas® Technology
- Precision digital PID valve control; no manual adjustment or tuning required
- Control valve with large flow coefficient (Cv) for precise control at low ΔP
- Patented, inherently linear Laminar Flow Element (LFE)
- Advanced platinum sensor technology
- All 316 stainless steel construction
- Unique Pilot Module (mounted or handheld) lets you view and change critical control functions including:
 - Gas type
 - Setpoint value
 - Zero value
 - Span value
 - Engineering units
 - Output signals
 - Full scale adjust
- Avoid recalibration by re-zeroing and re-spanning in the field
- Choose from multiple analog or digital signals including: RS-232, RS-485, 4-20 mA, 0-5, 1-5, 0-10 VDC
- Optional CompodTM adds MODBUS RTU multi-drop capability
- Primary standard calibration, NISTtraceable certification





DESCRIPTIONS

hen you need precise mass flow control of expensive process gases, where minimal pressure drop is a key consideration for cost savings and efficiency, the SmartTrak® 140 controls up to 500 slpm with an ultralow ΔP of 4.5 psid (310 mBard), much better than typical ΔP values of 25 psid (1700 mBard) for equivalent mass flow controllers on the market. Precision digital PID valve control means no manual adjustment or tuning.

The SmartTrak 140 mass flow controller is a hybrid of two innovative Sierra technologies: our award winning SmartTrak® 100 Series with its industry leading SmartTrak Laminar Flow Element (LFE), sensor and digital electronics is combined with our SideTrak® 840 low ΔP valve featuring large flow coefficient (Cv). By combining these two technologies, the SmartTrak 140 boasts the smallest pressure drop in the industry and includes all the features of Sierra's flagship SmartTrak 100 Series. Dial-A-Gas® Technology allows users to set zero, span, and full scale for 10 different gases independently in the field. A hand-held or instrument-mounted user display/interface called the Pilot Module makes field-adjustments and re-configuration easy.

Precision gas mass flow control at higher flow rates, typically greater than 300 slpm (nlpm), relies on a large pressure differential (ΔP) across the control valve, especially with the small flow bodies and control valves commonly used in capillary-type thermal mass flow controllers. In all cases, especially with expensive high purity gases used in the semiconductor industry, maintaining initial pressurization of the gas is critical until it is eventually put to work in the tool. This is where the reduction of functional efficiency and resulting financial losses can occur. The SmartTrak 140 was specifically designed to improve efficiency in these types of applications.

So, when you need premium high performance mass flow control, but require the absolute lowest possible pressure drop, think SmartTrak 140.





PERFORMANCE SPECIFICATIONS

Accuracy

Standard: +/- 1.0 % of full scale (including linearity) at operating conditions

Dial-A-Gas

+/- 1.0 % of full scale in all 10 standard gases (see chart below)

Repeatability

+/- 0.2% of full scale

Temperature Coefficient

+/- 0.025% of full scale per °F (± 0.05% of full scale per °C) or better

Pressure Coefficient

 \pm -0.01% of full scale per psi (\pm 0.15% of full scale per bar) or better

Response Time

600 millisecond time constant; 4 seconds (typical) to within +/- 2.0% of final value

OPERATING SPECIFICATIONS

Mass Flow Rates

0 to 500 slpm

Control Range

2 to 100% of full scale flow; automatic shut-off at 1.9%

Flow ranges specified are for an equivalent flow of nitrogen at 760 mm Hg and 21°C (70°F); other ranges in other units are available (e.g., nlpm, scfh, Nm3/h, Kg/h)

Gases

Measures and controls all clean gases including corrosives and toxics; specify when ordering.

The following ten gases make up the Dial-A-Gas feature of every SmartTrak instrument; up to nine alternate gases may be substituted.

Dial-A-Gas Flow Rates		
Gas	Max Flow Rate (slpm/nlpm)	
Air	500	
Argon (Ar)	725	
Carbon Dioxide (CO ₂)	370	
Carbon Monoxide (CO)	500	
Methane (CH ₄)	360	
Helium (He)	727	
Hydrogen (H ₂)	500	
Oxygen (O ₂)	500	
Nitrogen (N ₂)	500	
Nitrous Oxide (N ₂ O)	355	

OPERATING SPECIFICATIONS (continued)

Gas and Ambient Temperature

32 to 122°F (0 to 50°C)

Gas Pressure

500 psig (34 barg) maximum

Pressure Drop

Minimum Pressure Drop (ΔP)		
Flow Rate (slpm/nlpm)	ΔP (psid)	ΔP (mBard)
100	7.0	483
150	6.0	414
200	5.5	379
250 to 500	4.5	310

Leak Integrity

5 X 10⁻⁹ atm cc/sec of helium or better

Power Requirements (ripple should not exceed 100 mV peak-to peak) 24 VDC +/-10%, (800 mA, regulated)

Output Signal

Analog:

Linear 0/4–20 mA, 500 ohms maximum loop resistance and one of the following (user selectable): Linear 0–5 VDC, 1000 ohms minimum load resistance Linear 0-10 VDC, 1000 ohms minimum load resistance Linear 1-5 VDC, 1000 ohms minimum load resistance

Digital:

RS-232 standard, RS-485 optional Pilot Module Display optional

Command Signal

Analog (choice of one):

Linear 4-20 mA, 0-5 VDC, 0-10 VDC, 1-5 VDC

Digital:

RS-232 standard, RS-485 optional Pilot Module Display optional

Wetted Material

316 stainless steel or equivalent; 416 stainless steel; Viton or Neoprene "O" rings and Viton, Neoprene or Kalrez valve seat

OPTIONAL COMPOD

RS-485 communication with MODBUS RTU protocol allows digital multi-drop networks

Available with optional LCD display


Internal gas flow totalizer with adjustable pulse output


Two digital outputs and one analog input can be configured by user with MODBUS or included software for a wide variety of process controls




PHYSICAL DIMENSIONS (continued)

All dimensions are in inches with (mm) in brackets. Certified drawings are available on request. NOTE: Fittings are 1/2-inch compression.







ORDERING INFORMATION

PARENT NUMBER C140M Mass Flow Controller (up to 500 slpm, ΔP of 4.5 psid; 310 mBard)	
PILOT MODULE DISPLAY/INTERFACE NR No display/interface DD Pilot Module display/interface RD Remote display Pilot Module display/interface CMNR Compod™ with RS-485 MODBUS communication odisplay CMDD Compod™ with RS-485 MODBUS communication odisplay CMNRRelays CMNR with 2 analog relays CMDDRelays CMDD with 2 analog relays	
INLET/OUTLET FITTINGS 3 3/8-inch compression (maximum 300 slpm) 4 1/2-inch compression 6 1/2-inch VCO 11 10 mm compression 12 12 mm compression 13 1/4-inch FNPT adapter bushing (maximum 400 slpm) 14 3/8-inch FNPT (maximum 300 slpm) 15 1/2-inch FNPT	
ELASTOMERS OV1 Viton® ON1 Neoprene®	
VALVE SEAT SV1 Viton® or equivalent SN1 Neoprene® SK2 Kalrez®	
INPUT POWER PV2 24 VDC	
OUTPUT SIGNAL V1 0-5 VDC and 4-20 mA linear output signals V2 1-5 VDC and 4-20 mA linear output signals V3 0-10 VDC and 4-20 mA linear output signals	
SO Pilot Module/RS-232 (standard for digital operation) S1 0-5 VDC, linear S2 1-5 VDC, linear S3 0-10 VDC, linear S4 4-20 mA, linear S5 0-20 mA, linear	
C10 10-foot (3 m) communication cable C0 15-pin mating connector with no cable C1 6-inch (150mm) cable C3 3-foot (1m) cable C25 25-foot (8 m) communication cable C() Custom length communication cable. Specify cable le	ength in feet in parenthesis. Maximum length 50 feet (16 meters). Same

FOR ACCESSORIES AND ADDITIONAL CABLES PLEASE CONTACT YOUR LOCAL SIERRA DISTRIBUTOR